



Port list

No	Size	Connection	Usage
a	2" (ø51)	Tri-clamp	wort outlet
b	DN350		manhole
c	ø38		breath port
d	1.5" (ø38)	Tri-clamp	CIP
e	DN80	male	sight lamp
f	ø10		PT100
J <sub>1-2</sub>	1" (ø25)	Tri-clamp	Level gauge

Technical requirement

1. Total volume: 1620L, effective volume: 1500L;
2. Welding adopts argon arc welding;
3. The inner tank is polished to 0.6 μm, pickled and passivated to smooth and clean without dead corners, and the welding seam is polished with sanding tape;
4. After the production, the cylinder is filled with water to test for leaks.

